



## Using the lifting mechanism



High van Mercedes Benz V, leather cover plate.



Higher passenger car Renault Captur.



Application for lifting from seat to stand, AUDI A6.

- **Multi-purpose mechanism** that can be used in more applications: lifting transfer desk, sit-to-stand aid (myopat).
- Depending on the purpose we manufacture the end part which we prepare as needed, or you can finalize yourself.
- The mechanism is attached to the central body column.
- Very small installation dimensions, particularly small thickness.
- We can prepare stroke length of the device as needed. Standard **stroke lengths** are 250 and 435 mm. The Lower stroke lift is sufficient for most passenger cars, the higher stroke lift for vans.
- The overall dimensions are: height 470/635, width 123, thickness 48 mm.
- We are able to adapt your specific requirements or the specifics of your market.



HURT s. r. o. - Car Adaptations for Handicapped Bambousek 664 281 26 Týnec nad Labem CZECH REPUBLIC Tel.: +420 608 977 274 Email: info@hurt-auto.cz



EUROPEAN

MOBILITY GROUP